

LIGHT CAN BE PLACED AT ANY DISTANCE FROM HOLOGRAM ALONG THE LINE THAT HOLDS THIS ANGLE

Suggested light source is an MR16 Halogen Bulb. We use a 75 watt EYF narrow spot in a plug in can or a 100 watt Q100MR16EN in a 120 volt screw in can.

LIGHT SOURCE

HOLOGRAM

This is the height we have most often used as an average height. It may be changed if the average viewer in your case is taller or shorter.

THESE ARE APPROXIMATE SPECS FOR HOLOGRAM (light at ~45 degree angle)

